# DOWEX UPCORE Mono C-600

## A Uniform Particle Size Strong Acid Cation Exchange Resin Specifically Designed for the UPCORE System

Product	Туре	Matrix	Functional group
DOWEX* UPCORE* Mono C-600	Strong acid cation	Styrene-DVB, gel	Sulfonic acid
Guaranteed Sales Specifications		Na <sup>+</sup> form	H <sup>+</sup> form
Total exchange capacity, min.	eq/l	2.0	1.8
	kg/ft <sup>3</sup> as CaCO	3 43.7	39.3
Water content	%	42 - 48	50 - 56
Bead size distribution <sup>+</sup>			
Mean particle size	μm	585±50	600±50
Uniformity coefficient, max.	%	1.1	1.1
>850 µ, max.	%	5	5
<300 µ, max.	%	0.5	0.5
Whole uncracked beads, min.	%	95	95

Typical Physical and Chemical Properties		Na <sup>+</sup> form	H <sup>+</sup> form
Total swelling (Na <sup>+</sup> $\rightarrow$ H <sup>+</sup> )	%	8	8
Particle density	g/ml	1.28	1.22
Shipping weight	g/l Ibs/ft³	820 51	800 50

Recommended Operating Conditions	
Maximum operating temperature	120°C (250°F)
pH range	0-14
Bed depth, min.	1200 mm (4 ft)
Pressure drop, design max.	1.5 bar (22 psi)
Pressure drop, max.	2.5 bar (37 psi)
Flow rates: Service/fast rinse Regeneration/displacement rinse	5-60 m/h (2-24 gpm/ft²) 5-20 m/h (2-8 gpm/ft²)
Total rinse requirement	1-3 Bed volumes
Regenerant	8-12% NaCl, 4-6% HCl, 1-4% H <sub>2</sub> SO <sub>4</sub>

<sup>†</sup>For additional particle size information, please refer to the Particle Size Distribution Cross Reference Chart (Form No. 177-01775/CH 171-476-E).


#### Typical properties and applications:

DOWEX\* UPCORE\* Mono C-600 strong acid cation exchange resin is a uniform particle size resin specifically designed for use in the UPCORE packed bed counter-current regeneration system. It is well suited for use in both demineralization and softening applications. DOWEX UPCORE Mono C-600 resin has a smaller average particle diameter than conventional polydispersed cation resin. Its smaller, uniform size enhances operating capacity and regeneration efficiency while maintaining a moderate pressure drop. DOWEX UPCORE Mono C-600 resin also has outstanding resistance to attrition due to compressive and osmotic stress.

#### Packaging

25 liter bags or 5 cubic feet fiber drums.

### Figure 1. Pressure Drop Data



#### For other temperatures use:

 $\begin{array}{l} \mathsf{P}_{\mathsf{T}} = \mathsf{P}_{20^\circ \mathsf{C}} \ / \ (0.026 \ T_{^\circ \mathsf{C}} \ + \ 0.48), \ \text{where} \ \mathsf{P} \equiv bar/m \\ \mathsf{P}_{\mathsf{T}} = \mathsf{P}_{68^\circ \mathsf{F}} \ / \ (0.014 \ T_{^\circ \mathsf{F}} \ + \ 0.05), \ \text{where} \ \mathsf{P} \equiv psi/ft \end{array}$ 

**Warning:** Oxidizing agents such as nitric acid attack organic ion exchange resins under certain conditions. This could lead to anything from slight resin degradation to a violent exothermic reaction (explosion). Before using strong oxidizing agents, consult sources knowledgeable in handling such materials.

**Notice**: No freedom from any patent owned by Seller or others is to be inferred. Because use conditions and applicable laws may differ from one location to another and may change with time, Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other governmental enactments. Seller assumes no obligation or liability for the information in this document. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED.

Published September 1998.

Lenntech bv Rotterdamseweg 402m 2629HH Delft info@lenntech.com www.lenntech.com Tel. +31-15-261.09.00 Fax. +31-15-261.62.89